


# **Insulating Bushings - Knockout**

Images





Download Photo Image Dimension A in Inches: 1-15/16 Dimension B in Inches: 2-5/8 Dimension C in Inches: 2-1/2

**Download Dimensional Image** 

Application

Converts metallic box rough edged knockout holes to smooth insulated holes for protection of electrical and telecommunications cable. Rated 105 Degrees C.

## **Product Information**

Material: Plastic Finish: Natural

### **Certifications & Codes:**

CSA File Number: NEMA Standard: UL Standard: UNSPSC:

LR24719 FB-1 UL-514B 39121312

### Catalog ID: 9796

UPC Number: 781747007964

Description: Bushing, Insulating, Plastic Rated 105 Degrees C, 2.500 Inch Hole Dia.

Application: Converts metallic box rough edged knockout holes to smooth insulated holes for protection of electrical and telecommunications cable. Rated 105 Degrees C.

Trade Size: 2"

Country of Manufacture: USA

Std Pkg Qty: 100

Unit Qty: 20

#### **Bridgeport Fittings Inc.** 705 Lordship Blvd. Stratford, CT 06615

Phone: 203-377-5944 Fax: 203-381-3488