



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



984200604 14/2 FPL Unshielded Red

Southwire Company

Catalog Number	984200604
Manufacturer	Southwire Company
Description	Fire Alarm Cable, FPLR (UI), CMG/FT4 (Cul), Multi Conductor Type; 1000 FT; 0.194 Inch Outer Diameter; Bare Copper Conductor Material; UI 1424, Cul Approval; 300 V Voltage Rating; -20 to 60 Deg C Temperature Rating; 35.2 LB/MFT Weight; 2 Conductor(S)
Weight per unit	0.0400 (lbs/ft)
Product Category	Non-Plenum Unshielded Cable

Features

Conductor Size	14 AWG
Number of Conductors	2
Shielding Type	Non-Shielded
Stranding	SOLID
Voltage Rating	300 V

Material, Color, and Finish

Color Code	BLACK, RED
Conductor Material	Bare Copper
Insulation Material	PVC
Jacket Color	RED
Jacket Material	SUN RESISTANT PVC

Dimensions and Weight

Length	1000 ft
Outer Diameter	0.194 Inch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Additional Information	ROHS Compliant; Applicable Standard NEC 760; Insulation Thickness 0.008 Inch; Jacket Thickness 0.017 Inch; Insulated Conductor Diameter 0.08 Inch; Application Fire Alarm, Signaling, Smoke Detector, Fire Protective Circuit
Commodity Description	Non-Plenum Unshlded Multicond Cable
Description	14/2 FPL UNSHIELDED RED
extra long description	FPLR (UL), CMG/FT4 (CUL), MULTI CONDUCTOR TYPE; 1000 FT; 0.194 INCH OUTER DIAMETER; BARE COPPER CONDUCTOR MATERIAL; UL 1424, CUL APPROVAL; 300 V VOLTAGE RATING; -20 TO 60 DEG C TEMPERATURE RATING; 35.2 LB/MFT WEIGHT; 2 CONDUCTOR(S); PVC INSULATION MATERIAL; 14 AWG CONDUCTOR SIZE; BLACK, RED COLOR CODE; SUN RESISTANT PVC JACKET MATERIAL; REEL PACKAGE TYPE; SOLID STRANDING; RED JACKET COLOR; NON-SHIELDED SHIELDING TYPE; SIGNAL[R] BRAND; ROHS COMPLIANT; APPLICABLE STANDARD NEC 760; INSULATION THICKNESS 0.008
Long Description	FIRE ALARM CABLE, FPLR (UL), CMG/FT4 (CUL), MULTI CONDUCTOR TYPE; 1000 FT; 0.194 INCH OUTER DIAMETER; BARE COPPER CONDUCTOR MATERIAL; UL 1424, CUL APPROVAL; 300 V VOLTAGE RATING; -20 TO 60 DEG C TEMPERATURE RATING; 35.2 LB/MFT WEIGHT; 2 CONDUCTOR(S)
Product Type	Fire Alarm Cable

Manufacturer Information

Brand	Cables & Cords
Manufacturers Part Number	F60001-1A
Model	984

Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC CABLE
Type	FPLR (UL), CMG/FT4 (CUL), Multi Conductor

Packaging

Carton	1000
Package Type	Reel
Weight	35.2 Lb/MFt
Weight Per foot	0.04

Uses, Certifications, and Standards

Approval	UL 1424, CUL
Temperature Rating	-20 TO 60 DEG C