

CATV Coaxial Cables



992118

RG6 Tri-Shield CATV Coax Cables

| Part Number | Description | AWG | UL Type | Weight (Nom.) | Outside Dia. (Nom.) | Packaging | Jacket Color |
|-------------|---|--------|---------|---------------|---------------------|-------------------------------------|--------------|
| 992118 | RG6 18CCS 80%AL Tri-Shield - Tested to 3.0GHz | 18 CCS | CM CL2 | 31 lbs | 0.288" | 1,000' Reel (06) 1,000' Box (46) | Black (08) |



92003

RG6 Dual Shield CATV Coax Cables

| Part Number | Description | AWG | UL Type | Weight (Nom.) | Outside Dia. (Nom.) | Packaging | Jacket Color |
|-------------|--|--------------|----------|---------------|---------------------|-------------------------------------|--------------------------|
| 92001 | RG6 18CCS 40%AL - Tested to 3.0GHz | 18 CCS | CM CL2 | 26 lbs | 0.269" | 1,000' Reel (06) 1,000' Box (46) | Black (08) |
| 992128 | RG6 18CCS 40%AL - Tested to 3.0GHz 2x Dual (siamese) construction | 18 CCS | CM CL2 | 52 lbs | 0.269" x 0.503" | 1,000' Reel (06) | Black (08) |
| 92008 | RG6 18CCS Value Coax - Tested to 3.0GHz | 18 CCS | CM CL2 | 26 lbs | 0.269" | 1,000' Reel (06) 1,000' Box (46) | White (01) Black (08) |
| 92003 | RG6 18CCS 60%AL - Tested to 3.0GHz | 18 CCS | CM CL2 | 26 lbs | 0.269" | 1,000' Reel (06) 1,000' Box (46) | White (01) Black (08) |
| 92083 | RG6 18CCS 60%AL - Tested to 3.0GHz CMG FT-4 rated for Canada | 18 CCS | CM CL2 | 28 lbs | 0.269" | 1,000' Box (46) | White (01) Black (08) |
| 920036 | RG6 18CCS 60%AL - Tested to 3.0GHz Riser Rated | 18 CCS | CMR CL2R | 28 lbs | 0.269" | 1,000' Reel (06) 1,000' Box (46) | Black (08) |
| 921015 | RG6 18CCS 80%AL - Tested to 3.0GHz Plenum Rated | 18 CCS | CMP CL2P | 26 lbs | 0.228" | 1,000' Reel (06) | White (01) |
| 921009 | RG6 18BC 80%AL - Tested to 3.0GHz Plenum Rated | 18 BC | CMP CL2P | 26 lbs | 0.228" | 1,000' Reel (06) | White (01) |
| 921007 | RG6 18BC 90%AL - Tested to 3.0GHz Plenum Rated | 18 BC | CMP CL2P | 27 lbs | 0.233" | 1,000' Reel (06) | White (01) |
| 992479 | RG6 18CCS 60%AL - Tested to 3.0GHz For direct burial use (flooded) | 18 CCS | n/a | 27 lbs | 0.269" | 1,000' Reel (06) | Black (08) |
| 992481 | RG6 18CCS 60%AL - Tested to 3.0GHz 2x Dual (siamese) construction w/17 AWG steel mess. for aerial applications | 18 CCS | n/a | 67 lbs | 0.271" x 0.735" | 1,000' Reel (06) | Black (08) |



92009

RG59 Budget CATV Coax Cables

| Part Number | Description | AWG | UL Type | Weight (Nom.) | Outside Dia. (Nom.) | Packaging | Jacket Color |
|-------------|------------------|--------|---------|---------------|---------------------|-------------------------------------|--------------|
| 992101 | RG59 20CCS 40%AL | 20 CCS | CM CL2 | 22 lbs | 0.239" | 1,000' Box (46) | Black (08) |
| 992109 | RG59 20CCS 67%AL | 20 CCS | CM CL2 | 23 lbs | 0.239" | 1,000' Box (46) | Black (08) |
| 92006 | RG59 22CCS 40%AL | 22 CCS | CM CL2 | 20 lbs | 0.239" | 1,000' Reel (06) 1,000' Box (46) | Black (08) |
| 92009 | RG59 22CCS 65%AL | 22 CCS | CM CL2 | 21 lbs | 0.239" | 1,000' Reel (06) 1,000' Box (46) | Black (08) |

Packaging Options

Coleman Cable offers four types of packaging options.

- Signa-Coil
- Reel-in-box
- Pull-out box (Rabbit pull)
- Reels


All provide fast and easy cable access. Kinks and twists are eliminated. You get tangle-free cable delivery each and every time. These durable, compact designs save on installation time while reducing waste and material costs. They can be easily stacked to save room.

* Not all options are available for each product



Coleman Cable Part Legend

XXXXXX-XX-XX



Put-ups

| Put-ups | Code |
|--------------------------------|------|
| Reel, 250 ft | 04 |
| Reel, 500 ft | 05 |
| Reel, 1,000 ft | 06 |
| Reel-in-box, 1,000 ft | 16 |
| RabbitPull™ Pull-Box, 500 ft | 45 |
| RabbitPull™ Pull-Box, 1,000 ft | 46 |
| SignaCoil™ 500 ft | 55 |
| SignaCoil™ 1,000 ft | 56 |

Colors

| Colors | Code | Colors | Code |
|--------|------|-------------|------|
| White | 01 | Pink | 11 |
| Yellow | 02 | Purple | 13 |
| Orange | 03 | Clear | 18 |
| Red | 04 | Fluorescent | 21 |
| Green | 05 | Pink | 21 |
| Blue | 06 | Ivory | 22 |
| Brown | 07 | Natural | 23 |
| Black | 08 | Beige | 33 |
| Gray | 09 | Red Striped | 44 |
| | | CorraClad™ | 44 |

