

#12 Solid Insulated Copper Wire Pigtail, 8 in. Length (25/BE)

By Raco Catalog # 996

#12 Solid Insulated Copper Wire Pigtail, 8 in. Length (25/BE)

Features

- RACO[®] 6" and 8" ground pigtails feature 4-way slotted, phillips, hex-head) combo 10-32 captive screws
- #12 solid insulated copper wire
- Captive four-way combo head ground screw
- 8 in. wire length
- Suitable for 10-32 threaded hole

General

Box
Contact Manufacturer
996
Ground Screws
050169009963



Dimensions

Dimensions	8 in x 0.4 in x 0.5 in
Height	0.5 in
Length	8 in
Weight	0.022 lb
Width	0.4 in

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Packaging Type	Bundle
Pallet Quantity	80000

Product Assets

Catalogs - RACO / TayMac / Bell Full Catalog SDS - HCC_SDS Terms and Conditions - HCC Terms & Conditions



©2024 Hubbell Incorporated. All rights reserved. RACO-996-SPEC-EN | REV 5/2024