



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A1008CHNFSS6 10X8X4 N4X SS6 CH Clamp CVR

Hoffman Enclosures, Inc.

Catalog Number	A1008CHNFSS6
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge With Clamps Junction Box Type 4X, 10X8X4, Brushed, Stainless 316
Weight per unit	7.6 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

ip rating	IP66
Material	Stainless Steel 316L

Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4

Dimensions and Weight

Depth	4
Size	10.00x8.00x4.00 in
Width	8

Descriptions

Description	10X8X4 N4X SS6 CH CLAMP CVR
extra long description	NVENT HOF A1008CHNFSS6 Stainless CH
Features	Used in either indoor or outdoor applications, these enclosures combine a rugged continuous hinge, seamless foam-in-place gasket and stainless steel screw-down clamps for a reliable seal that protects components from corrosive environments.
Long Description	Continuous Hinge with Clamps Junction Box Type 4X, 10x8x4, Brushed, Stainless 316
Product Type	Stainless CHNFSS Box 10.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510834203
Manufacturers Part Number	A1008CHNFSS6
UPC	783510834203

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Industrial Terminal and Junction Boxes



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	4
Weight Per each	7.6

Uses, Certifications, and Standards

Application	Corrosive Environments; Controls and Drives
nema rating	4X Watertight, corrosion-resistant