



A101072RT 10X10X72 N3R WR TR

Hoffman Enclosures, Inc.

Catalog Number	A101072RT
Manufacturer	Hoffman Enclosures, Inc.
Description	Wiring Trough Nema Type 3R, 10.00X10.00X72.00, Gray, Steel
Weight per unit	75.0 (lbs/each)
Product Category	Nema Type 3R Trough & Gutter

Features

ip rating	IP32
Material	Mild Steel;Steel

Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Galvanized

Dimensions and Weight

Depth	72
Size	10.00x10.00x72.00 in
Width	10

Descriptions

Description	10X10X72 N3R WR TR
extra long description	NVENT HOF A101072RT Wire Trough, Ty
Features	Screw-Cover Wiring Trough, Type 3R is used for protecting wire and cable distribution, junctions and terminations in outdoor applications that may be exposed to wet conditions. A Padlock Hasp Kit can be installed for increased security.
Long Description	Wiring Trough NEMA Type 3R, 10.00x10.00x72.00, Gray, Steel
Product Type	Wire Trough, Type 3R

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510430399
Manufacturers Part Number	A101072RT
UPC	783510430399

Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	Commercial Wiring Troughs;Trough

Packaging

Carton	1
Weight Per each	75



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

nema rating

Power Distribution

3R Weather-resistant, except dust