



A1212CHNFSS 12X12X6 N4X CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A1212CHNFSS
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge With Clamps Junction Box Type 4X, 12X12X6, Brushed, Stainless 304
Weight per unit	27.0 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

ip rating	IP66
Material	Stainless Steel;Stainless Steel 304

Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4

Dimensions and Weight

Size	12.00x12.006.00 in
Width	12

Descriptions

Description	12X12X6 N4X CH CLMP CVR
extra long description	NVENT HOF A1212CHNFSS Stainless CHN
Features	Used in either indoor or outdoor applications, these enclosures combine a rugged continuous hinge, seamless foam-in-place gasket and stainless steel screw-down clamps for a reliable seal that protects components from corrosive environments.
Long Description	Continuous Hinge with Clamps Junction Box Type 4X, 12x12x6, Brushed, Stainless 304
Product Type	Stainless CHNFSS Box 12.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510564605
Manufacturers Part Number	A1212CHNFSS
UPC	783510564605

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Terminal and Junction Boxes

Packaging

Carton	1
Package	2
Weight Per each	26.96



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2700 Summit Ave. Suite 200
75074-0000, TX Plano
Phone: 469-467-7771
Fax: 469-467-0282

Uses, Certifications, and Standards

Application

Controls and Drives; Corrosive Environments

nema rating

4X