



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A14128CHQRFGW 14X12X8 N4X FG WNDW CVR CH

Hoffman Enclosures, Inc.

Catalog Number	A14128CHQRFGW
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge QR Window Cover Enclosure 4X, 14X12X8, Light Gray, Fiberglass
Weight per unit	8.5 (lbs/each)
Product Category	Nema Types 4, 4X, 12 & 13

Features

ip rating	IP66
Material	Fiberglass

Material, Color, and Finish

Color	Light Gray
Color Code	RAL 7035
Finish	Smooth Matte

Dimensions and Weight

Depth	8
Height	14
Size	14.00x12.00x8.00 in
Width	12

Descriptions

Description	14X12X8 N4X FG WNDW CVR CH
extra long description	NVENT HOF A14128CHQRFGW Enclosure 1
Features	The efficient design and simple construction of these enclosures make them durable in corrosive environments, yet aesthetically pleasing. Corner latches provide unobstructed access. The continuous hinge provides a secure seal, and double latching creates added security.
Long Description	Continuous Hinge QR Window Cover Enclosure 4X, 14x12x8, Light Gray, Fiberglass
Product Type	Enclosure 14.00X12.00X8.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510312909
Manufacturers Part Number	A14128CHQRFGW
UPC	783510312909

Taxonomies, Classifications, and Categories

Category Description	VYNCKIER FIBERGLASS ENCLOSURES
Type	Window Cover, Quick Release



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	8.5

Uses, Certifications, and Standards

Application	Controls and Drives; Corrosive Environments
nema rating	4X Watertight, corrosion-resistant