



## A1412CHNFSS 14X12X6 N4X CH, CLMP LTCH

*Hoffman Enclosures, Inc.*

Catalog Number	A1412CHNFSS
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge With Clamps Junction Box Type 4X, 14X12X6, Brushed, Stainless 304
Weight per unit	30.1 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

### Features

ip rating	IP66
Material	Stainless Steel;Stainless Steel 304

### Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4

### Dimensions and Weight

Size	14.00x12.00x6.00 in
Width	12

### Descriptions

Description	14X12X6 N4X CH,CLMP LTCH
extra long description	NVENT HOF A1412CHNFSS Stainless CHN
Features	Used in either indoor or outdoor applications, these enclosures combine a rugged continuous hinge, seamless foam-in-place gasket and stainless steel screw-down clamps for a reliable seal that protects components from corrosive environments.
Long Description	Continuous Hinge with Clamps Junction Box Type 4X, 14x12x6, Brushed, Stainless 304
Product Type	Stainless CHNFSS Box 14.00

### Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510563004
Manufacturers Part Number	A1412CHNFSS
UPC	783510563004

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Terminal and Junction Boxes

### Packaging

Carton	1
Package	2
Weight Per each	30.08



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3440 Hwy 114 Suite 200  
76177-0000, TX Fort Worth  
Phone: 682-237-5470  
Fax: 682-237-5471

## Uses, Certifications, and Standards

Application

Controls and Drives; Corrosive Environments

nema rating

4X