



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2025 North Masch Branch Road Suite 105
76207-0000, TX Denton
Phone: 940-381-9070
Fax: 940-380-0325



A1614CHNFSS6 16X14X6 N4X CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A1614CHNFSS6
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge With Clamps Junction Box Type 4X, 16X14X6, Brushed, Stainless 316
Weight per unit	19.0 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

ip rating	IP66
Material	Stainless Steel;Stainless Steel 316L

Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4

Dimensions and Weight

Size	16.00x14.00x6.00 in
Width	14

Descriptions

Description	16X14X6 N4X CH CLMP CVR
extra long description	NVENT HOF A1614CHNFSS6 Stainless CH
Features	Used in either indoor or outdoor applications, these enclosures combine a rugged continuous hinge, seamless foam-in-place gasket and stainless steel screw-down clamps for a reliable seal that protects components from corrosive environments.
Long Description	Continuous Hinge with Clamps Junction Box Type 4X, 16x14x6, Brushed, Stainless 316
Product Type	Stainless CHNFSS Box 16.00
Short Description	Stainless CHNFSS Box 16.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510834609
Manufacturers Part Number	A1614CHNFSS6
UPC	783510834609

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Terminal and Junction Boxes

Packaging

Carton	1
Weight Per each	19



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2025 North Masch Branch Road Suite 105
76207-0000, TX Denton
Phone: 940-381-9070
Fax: 940-380-0325

Uses, Certifications, and Standards

Application	Controls and Drives; Corrosive Environments
nema rating	4X