



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A181610PHC 18.6X16.6X10.1 N4X SLD HC

Hoffman Enclosures, Inc.

Catalog Number	A181610PHC
Manufacturer	Hoffman Enclosures, Inc.
Description	Polypro Type 4X, 17.95X15.94X10.35, Polyester
Weight per unit	13.0 (lbs/each)
Product Category	Nema Type 1 Metallic Enclosure

Features

ip rating	IP66
Material	Polyester

Material, Color, and Finish

Color	Gray
Color Code	RAL 7035
Finish	Smooth Matte

Dimensions and Weight

Height	18.58
Size	17.95x15.94x10.35 in
Width	16.58

Descriptions

Description	18.6X16.6X10.1 N4X SLD HC
extra long description	NVENT HOF A181610PHC TYPE 4X POLY S
Features	PolyPro polyester enclosures perform exceptionally well in applications where harsh chemicals, weather extremes and corrosive environments demand toughness from a lightweight enclosure. Providing excellent ultraviolet protection and a tight environmental seal, these versatile, feature-rich enclosures are also recyclable.
Long Description	PolyPro Type 4X, 17.95x15.94x10.35, Polyester
Product Type	Type 4X Poly Solid CVR QR/SC
Short Description	TYPE 4X POLY SOLID CVR QR/SC

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510170813
Manufacturers Part Number	A181610PHC
UPC	783510170813

Taxonomies, Classifications, and Categories

Category Description	PVC BOXES
Type	Fiberglass and Thermoplastic Wall Mounted Industrial Enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	13

Uses, Certifications, and Standards

Application	Controls and Drives;Corrosive Environments
nema rating	4X