

Project:	Type:	Prepared By:	Date:
-----------------	--------------	---------------------	--------------



Features and Benefits

- Energy efficient replacement for incandescent and halogen lamps
- Constructed from durable plastic which lowers risk of breakage
- Rated for use in enclosed and open fixtures in dry or damp locations (>15W A19 is Open fixture rated)
- Frosted lens produces smooth diffuse light
- Longer lifespan compared to legacy equivalents minimizes replacement and maintenance costs
- ENERGY STAR Compliant
- Dimmable with common dimmer types (check compatibility list)

Technical Specifications	
Performance	L70 Lifespan:
Product Type:	15,000 Hours
A-Line	Dimmable:
Input Wattage:	Yes, down to 10%
10W	Construction
Typical Lumen Output:	Bulb Shape:
800	A19
Efficacy:	Base Type:
80 lm/W	E26
Color Temperature:	Beam Angle:
2700K Soft White	230°
CRI:	For Use Outdoors in Open Fixtures:
80	No
	Other
	Equivalency:
	60W Incandescent
	Warranty (Years):
	RAB warrants that our LED products will be free from defects in materials and workmanship for a period of three (3) years from the date of delivery to the end user, including coverage of light output, color stability, driver performance and fixture finish. RAB's warranty is subject to all terms and conditions found at rablighting.com/warranty .
	Electrical
	Power Factor:
	≥0.7
	Operating Temperature:
	-20°C - 45°C
	Input Voltage:
	120V

Technical Specifications (continued)

Electrical

Operating Frequency:

60 Hz

Electrical Characteristics

Input Current @ 120V:

101mA

Compliance

UL Listed:

Yes

ENERGY STAR V2.0:

This product is ENERGY STAR® Version 2.0 Certified

Energy Star ID:

2357502


CEC Status:

Not lawful for sale in California

Case and Pallet Dimensions

	QTY	LENGTH (in)	WIDTH (in)	HEIGHT (in)
CASE	12	15.4	5.2	4.9
PALLET	2268	47.2	39.4	45.7

Dimension



Light Distribution

