



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3723 Keystone Ave  
37211-0000, TN Nashville  
Phone: 629-262-0932  
Fax: 629-262-0933



## A1910E26840DIM 10W Led A19 40K 800LM Dim Rab Lighting

Catalog Number	A1910E26840DIM
Manufacturer	Rab Lighting
Description	A Line Bulbs 840 Lumens Led A19 10W 60EQ E26 CRI80 4000K Dimmable
Weight per unit	0.1323 (lbs/each)
Product Category	Led A-Line A Shape Lamps

### Features

average life	15000
Base	E26
beam angle	230
lumens	840
Power Factor	0.7
Shape	A19
Voltage Rating	120
Wattage	10

### Material, Color, and Finish

color rendering index (cri)	80 CRI
color temperature	4000

### Descriptions

Description	10W LED A19 40K 800LM DIM
extra long description	RAB A19-10-E26-840-DIM LED A19 10W
Long Description	A Line Bulbs 840 Lumens Led A19 10W 60Eq E26 CRI80 4000K Dimmable
Product Type	Led A19 10W 60EQ 840LM E26 4K Dim

### Manufacturer Information

Brand	RAB Lighting Inc
GTIN	00019813748214
Manufacturers Part Number	A19-10-E26-840-DIM
UPC	019813748214

### Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS
Type	Lamps

### Packaging

Carton	1
Package	12
Weight Per each	0.1323