

Project:	Type:	Prepared By:	Date:
-----------------	--------------	---------------------	--------------



Features and Benefits

- Replacement for conventional decorative lamps
- Filament LED construction gives a unique traditional look and feel for decorative and ambient applications
- Produces rich and vibrant colors, >90CRI
- Rated for use in enclosed and open fixtures in wet locations
- Longer lifespan compared to legacy equivalents minimizes replacement and maintenance costs
- Title 20 Compliant, ENERGY STAR Compliant, UL Listed
- Smooth uniform dimming down to 10% (check dimmer compatibility list)

Technical Specifications		
Performance	L70 Lifespan:	For Use Outdoors in Open Fixtures:
Product Type: Decorative	15,000 Hours	No
Input Wattage: 6W	Dimmable: Yes, down to 10%	Other
Typical Lumen Output: 810	Construction	Equivalency: 60W Incandescent
Efficacy: 90 lm/W	Bulb Shape: A19	Warranty (Years): RAB warrants that our LED products will be free from defects in materials and workmanship for a period of three (3) years from the date of delivery to the end user, including coverage of light output, color stability, driver performance and fixture finish. RAB's warranty is subject to all terms and conditions found at rablighting.com/warranty .
Color Temperature: 2700K Soft White	Finish: Clear	Electrical
CRI: 90	Base Type: E26	Power Factor: 0.7
	Beam Angle: 360°	Operating Temperature: -20°C - 45°C

Technical Specifications (continued)

Electrical

Input Voltage:

120V

Electrical Characteristics

Flicker:

<30%

Compliance

UL Listed:

Yes

ENERGY STAR V2.0:

This product is ENERGY STAR® Version 2.0 Certified

Energy Star ID:

2330359


CEC Status:

Lawful for sale in California

Case and Pallet Dimensions

	QTY	LENGTH (in)	WIDTH (in)	HEIGHT (in)
CASE	12	10.8	8.2	5.1
PALLET	1080	38.4	44	37.2

Dimension



Light Distribution

