

# Eaton A200M3CAC

Catalog Number: A200M3CAC

Eaton Freedom NEMA motor control starter, Non-Reversing Starter, 120V/60 Hz or 110V/50 Hz coil voltage, 90A, Three-pole, Size 3, 25 hp at 208V, 30 hp at 240V, 50 hp at 480,600V, A200 series, Wired for Separate Control



## General specifications

|                               |                             |
|-------------------------------|-----------------------------|
| <b>Product Name</b>           | <b>Catalog Number</b>       |
| Eaton A200 NEMA motor control | A200M3CAC                   |
| <b>UPC</b>                    | <b>Product Length/Depth</b> |
| 786678231259                  | 6.75 in                     |
| <b>Product Height</b>         | <b>Product Width</b>        |
| 6.9 in                        | 4.63 in                     |
| <b>Product Weight</b>         | <b>Certifications</b>       |
| 10.05 lb                      | UL Listed<br>CSA Certified  |

## Catalog Notes

For ambient compensated overload relay with auto-reset, add Suffix D.

[Accessories](#)

[Motor control](#)

[Catalogs](#)

[Eaton's Volume 5—Motor Control and Protection](#)

[Installation instructions](#)

[Instructions for A200, A210, A250 size 6, two- or three-pole non-reversing or reversing motor controllers](#)

[Specifications and datasheets](#)

[Eaton Specification Sheet - A200M3CAC](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)