

Eaton A200M3CX

Catalog Number: A200M3CX

Eaton Freedom NEMA motor control starter, Non-Reversing Starter, 480V/60 Hz coil voltage, 90A, Three-pole, Size 3, 25 hp at 208V, 30 hp at 240V, 50 hp at 480,600V, A200 series



General specifications

Product Name

Eaton A200 NEMA motor control

Catalog Number

A200M3CX

UPC

786678231297

Product Length/Depth

6.75 in

Product Height

4.63 in

Product Width

6.63 in

Product Weight

9.3 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed
CSA Certified

Catalog Notes

For ambient compensated overload relay with auto-reset, add Suffix D.

Accessories

Motor control

Phase

Three-phase magnetic

Size

3

Amperage rating

90A

Series

A200

Special features

Bulk Package

Horsepower

25 hp at 208 V, 30 hp at 240 V, 50 hp at 480/600 V

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Installation instructions

[Instructions for A200, A210, A250 size 6, two- or three-pole non-reversing or reversing motor controllers](#)

Specifications and datasheets

[Eaton Specification Sheet - A200M3CX](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia