

Eaton A200M4CAC

Catalog Number: A200M4CAC

Eaton Freedom NEMA motor control starter, Non-Reversing Starter, 120V/60 Hz or 110V/50 Hz coil voltage, 135A, Three-pole, Size 4, 40 hp at 208V, 50 hp at 240V, 100 hp at 480,600V, A200 series, Wired for Separate Control



General specifications

Product Name	Catalog Number
Eaton A200 NEMA motor control	A200M4CAC
UPC	Product Length/Depth
786678007199	6.75 in
Product Height	Product Width
4.63 in	6.63 in
Product Weight	Warranty
9.3 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	Catalog Notes
CSA Certified UL Listed	For ambient compensated overload relay with auto-reset, add Suffix D.

Accessories

Motor control

Phase

Three-phase magnetic

Size

4

Amperage rating

135A

Series

A200

Horsepower

40 hp at 208 V, 50 hp at 240 V, 100 hp at 480/600 V

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Installation instructions

[Instructions for A200, A210, A250 size 6, two- or three-pole non-reversing or reversing motor controllers](#)

Specifications and datasheets

[Eaton Specification Sheet - A200M4CAC](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)