

# Eaton A201107-3

Catalog Number: A201107-3

Eaton Crouse-Hinds series Roughneck E1049 plug contact, Up to 1135A continuous, 777 kcmil, Hexagon crimp or solder, Copper, Male, 1000 Vac/dc

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Roughneck E1049 plug contact	A201107-3
	UPC
	662275107381
Product Length/Depth	Product Height
6.5 in	22.32 in
Product Width	Product Weight
2.32 in	1.5 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

3

## Product specifications

### Cable size

777 kcmil

### Amperage Rating

Up to 1135A Continuous

### Voltage rating

1000 Vac/dc

### Gender

Male

### Connection type

Hexagon crimp or solder

### Contact material

Copper

## Resources

### Brochures

[Roughneck Single Pole High-amperage Plugs and Connectors brochure](#)

### Catalogs

[Roughneck Single Pole High Amperage Plugs and Connectors catalog page](#)

### Installation instructions

[IF 1777 - Roughneck E1049 Series Connectors](#)

[IF 1778 - Roughneck E1049 Series Connectors and Receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - A201107-3](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)