



A202006LP 20X20X6 N12 CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A202006LP
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge Enclosure With Clamps LP Type 4, 20X20X6, Gray, Mild Steel
Weight per unit	29.2 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Features

ip rating	IP66
Material	Steel

Material, Color, and Finish

Finish	Powder Coated
--------	---------------

Dimensions and Weight

Depth	6
Height	20
Size	20.00x20.00x6.00 in
Width	20

Descriptions

Description	20X20X6 N12 CH CLMP CVR
extra long description	NVENT HOF A202006LP Enclosure 20.00
Features	These single-door enclosures feature a hinged door with clamps on three sides to create a secure seal in indoor or outdoor environments. The gray polyester powder finish inside and out provides enhanced corrosion protection in outdoor applications.
Long Description	Continuous Hinge Enclosure with Clamps LP Type 4, 20x20x6, Gray, Mild Steel
Product Type	Enclosure 20.00X20.00X6.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510280406
Manufacturers Part Number	A202006LP
UPC	783510280406

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures

Packaging

Carton	1
Weight Per each	29.22



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1035 S. Graham St.
76401-0000, TX Stephenville
Phone: 254-965-8083
Fax: 254-968-2662

Uses, Certifications, and Standards

Application

Controls and Drives

nema rating

12