



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A20H16BLP 20X16X8 N4 CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A20H16BLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge Enclosure With Clamps LP Type 4, 20X16X8, Gray, Mild Steel
Weight per unit	27.8 (lbs/each)
Product Category	Nema Types 4 & 12 Metallic Enc

Features

ip rating	IP66
Material	Steel

Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Powder Coated

Dimensions and Weight

Depth	8
Height	20
Size	20.00x16.00x8.00 in
Width	16

Descriptions

Description	20X16X8 N4 CH CLMP CVR
extra long description	NVENT HOF A20H16BLP Type 4 Encl. 20
Features	These single-door enclosures feature a hinged door with clamps on three sides to create a secure seal in indoor or outdoor environments. The gray polyester powder finish inside and out provides enhanced corrosion protection in outdoor applications.
Long Description	Continuous Hinge Enclosure with Clamps LP Type 4, 20x16x8, Gray, Mild Steel
Product Type	Type 4 Encl. 20.00X16.00X8.00
Short Description	Type 4 Encl. 20.00x16.00x8.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510244200
Manufacturers Part Number	A20H16BLP
UPC	783510244200

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status Inactive

Packaging

Carton 1

Weight Per each 27.82

Uses, Certifications, and Standards

Application Controls and Drives

nema rating 12