



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5510 West 65th Street
72209-0000, AR Little Rock
Phone: 501-565-1785
Fax: 501-565-0827



A242408LP 24X24X8 N12 CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A242408LP
Manufacturer	Hoffman Enclosures, Inc.
Description	Wall-Mount Enclosure, Steel, Type 12 Continuous Hinge, Wall Mount, White (Inside);Ansi 61 Gray (Outside), White (Inside);Gray (Door), 24 In Overall Width, 24 In Overall Length, 8 In Overall Height, 43 LB
Weight per unit	43.0 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Material, Color, and Finish

Finish	Powder Coated
--------	---------------

Dimensions and Weight

Depth	8
Height	24
Size	24.00x24.00x8.00 in
Width	24

Descriptions

Description	24X24X8 N12 CH CLMP CVR
extra long description	NVENT HOF A242408LP Encl Cont Hng C
Features	These single-door enclosures feature a hinged door with clamps on three sides to create a secure seal in indoor or outdoor environments. The gray polyester powder finish inside and out provides enhanced corrosion protection in outdoor applications.

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510282103
UPC	783510282103

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures

Packaging

Carton	1
Weight Per each	43

Uses, Certifications, and Standards

nema rating	12
-------------	----