ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A242410LP 24X24X10 N12 CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A242410LP
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge Enclosure With Clamps LP Type 4, 24X24X10, Gray, Mild Steel
Weight per unit	53.0 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Features

ip rating	IP66
Material	Steel

Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Powder Coated

Dimensions and Weight

Depth	10
Height	24
Size	24.00x24.00x10.00 in
Width	24

Descriptions

Description	24X24X10 N12 CH CLMP CVR
extra long description	NVENT HOF A242410LP Enclosure 24.00
Features	This single-door enclosure solution has been redesigned to achieve a universal rating, with the enclosure suitable for both indoor and outdoor applications. All hardware is stainless steel, including the screw-down door clamps and heavy-gauge hinge pin. The door clamp count and position has been re-defined to achieve optimal compression of the seamless, foam-in-place gasket. As with many nVent HOFFMAN enclosure solutions, this solution is finished both inside and out in a premium, polyester powder paint th
Long Description	Continuous Hinge Enclosure with Clamps LP Type 4, 24x24x10, Gray, Mild Steel
Product Type	Enclosure 24.00X24.00X10.00
Short Description	Enclosure 24.00x24.00x10.00

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510284008
Manufacturers Part Number	A242410LP
UPC	783510284008

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures

Packaging

Carton	1
Weight Per each	53

Uses, Certifications, and Standards

Application	Controls and Drives
nema rating	12