



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

411 Autumn Street
71901-0000, AR Hot Springs
Phone: 501-762-8210
Fax: 501-762-8211



A242412LP 24X24X12 N12 CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A242412LP
Manufacturer	Hoffman Enclosures, Inc.
Description	Wall-Mount Enclosure, Steel, Type 12 Continuous Hinge, Wall Mount, White (Inside);Ansi 61 Gray (Outside), White (Inside);Gray (Door), 24 In Overall Width, 24 In Overall Length, 12 In Overall Height, 58 LB
Weight per unit	58.0 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Material, Color, and Finish

Finish	Powder Coated
--------	---------------

Dimensions and Weight

Depth	12
Height	24
Size	24.00x24.00x12.00 in
Width	24

Descriptions

Description	24X24X12 N12 CH CLMP CVR
extra long description	NVENT HOF A242412LP Enclosure 24.00
Features	These single-door enclosures feature a hinged door with clamps on three sides to create a secure seal in indoor or outdoor environments. The gray polyester powder finish inside and out provides enhanced corrosion protection in outdoor applications.

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510285203
UPC	783510285203

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures

Packaging

Carton	1
Weight Per each	58

Uses, Certifications, and Standards

nema rating	12 Indoor, dust-resistant
-------------	---------------------------