ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
3168 SW Loop 436
75633-0000, TX Carthage
Phone: 903-694-9924
Fax: 903-694-9928



A242412LP 24X24X12 N12 CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A242412LP
Manufacturer	Hoffman Enclosures, Inc.
Description	Wall-Mount Enclosure, Steel, Type 12 Continuous Hinge, Wall Mount, White (Inside);Ansi 61 Gray (Outside), White (Inside);Gray (Door), 24 In Overall Width, 24 In Overall Length, 12 In Overall Height, 58 LB
Weight per unit	58.0 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Material, Color, and Finish

Color Code	ANSI 61
Finish	Powder Coated

Dimensions and Weight

Depth	12
Height	24
Size	24.00x24.00x12.00 in
Width	24

Descriptions

Description	24X24X12 N12 CH CLMP CVR
extra long description	NVENT HOF A242412LP Enclosure 24.00
Features	This single-door enclosure solution has been redesigned to achieve a universal rating, with the enclosure suitable for both indoor and outdoor applications. All hardware is stainless steel, including the screw-down door clamps and heavy-gauge hinge pin. The door clamp count and position has been re-defined to achieve optimal compression of the seamless, foam-in-place gasket. As with many nVent HOFFMAN enclosure solutions, this solution is finished both inside and out in a premium, polyester powder paint th

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510285203
UPC	783510285203

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures

Packaging

Carton	1
Weight Per each	58

3168 SW Loop 436
75633-0000, TX Carthage
Phone: 903-694-9924
Fax: 903-694-9928

Uses, Certifications, and Standards

nema rating	12