



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3448 Sherwood Way
76901-0000, TX San Angelo
Phone: 325-944-7321
Fax: 325-944-1579



A24H2408GQRLP 24.19X24.19X8 N4X FG QRL

Hoffman Enclosures, Inc.

Catalog Number	A24H2408GQRLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Hinge Cover Enclosure Quick-Release Type 4X, 24.19X24.19X8.00, Gray, Fiberglass
Weight per unit	29.0 (lbs/each)
Product Category	Nema Types 4, 4X, 12 & 13

Features

ip rating	IP66
-----------	------

Material, Color, and Finish

Color	Gray
Finish	Smooth Matte

Dimensions and Weight

Depth	8
Height	24.19
Size	24.19x24.19x8.00 in
Width	24.19

Descriptions

Description	24.19X24.19X8 N4X FG QRL
extra long description	NVENT HOF A24H2408GQRLP Enclosure 2
Features	A full range of modification options are available for wall-mount fiberglass enclosures, including variable depths to accommodate larger controls. These enclosures feature padlockable polyester latches, or HOFFMAN's exclusive PowerGlide Handle with 3-point latching, for ease of access with increased security.
Long Description	Hinge Cover Enclosure Quick-Release Type 4X, 24.19x24.19x8.00, Gray, Fiberglass
Product Type	Enclosure 24.19X24.19X8.00
Short Description	Enclosure 24.19x24.19x8.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510226404
Manufacturers Part Number	A24H2408GQRLP
UPC	783510226404

Taxonomies, Classifications, and Categories

Category Description	VYNCKIER FIBERGLASS ENCLOSURES
Type	Fiberglass and Thermoplastic Wall Mounted Industrial Enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3448 Sherwood Way
76901-0000, TX San Angelo
Phone: 325-944-7321
Fax: 325-944-1579

Packaging

Carton	1
Weight Per each	29

Uses, Certifications, and Standards

Application	Controls and Drives;Corrosive Environments
nema rating	4X