

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3205 Axtell 88101-0000, NM Clovis Phone: 575-742-2504

Fax: 575-742-2508



A24H2408SS6LP 24X24X8 N4X SS CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A24H2408SS6LP
Manufacturer	Hoffman Enclosures, Inc.
Description	Wallmount Hinged With Nema Clamps Type 4X, 24X24X8,
	Brushed, SS316
Weight per unit	51.0 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

ip rating IP66
Material Stainless Steel 316L

Material, Color, and Finish

Color Unpainted
Finish Brushed #4

Dimensions and Weight

Depth	8
Height	24
Size	24.00x24.00x8.00 in
Width	24

Descriptions

Description	24X24X8 N4X SS CH CLMP CVR
extra long description	NVENT HOF A24H2408SS6LP Stainless E
Features	For use in indoor and outdoor corrosive environments that require a water-tight seal, this enclosure's seamless foam-in-place gasket and screw-down clamps provide a secure seal against contaminants.
Long Description	Wallmount Hinged with NEMA Clamps Type 4X, 24x24x8, Brushed, SS316
Product Type	Stainless Encl. 24.00X24.00X8.

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510291105
Manufacturers Part Number	A24H2408SS6LP
UPC	783510291105

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Туре	Stainless Steel Wall Mounted Industrial Enclosures



ELLIOTT ELECTRIC SUPPLY 3205 Axtell 88101-0000, NM Clovis Phone: 575-742-2504 Fax: 575-742-2508

Packaging	
Carton	1
Weight Per each	51
Uses, Certifications, and Standards	
Application	Corrosive Environments; Controls and Drives
nema rating	4X Watertight, corrosion-resistant