



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5500 Wheeler Avenue
72901-0000, AR Fort Smith
Phone: 479-648-1902
Fax: 479-648-1960



A24H2412SS6LP 24X24X12 N4X SS CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A24H2412SS6LP
Manufacturer	Hoffman Enclosures, Inc.
Description	Wallmount Hinged With Nema Clamps Type 4X, 24X24X12, Brushed, SS316
Weight per unit	59.0 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

ip rating	IP66
Material	Stainless Steel;Stainless Steel 316L

Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4

Dimensions and Weight

Depth	12
Height	24
Size	24.00x24.00x12.00 in
Width	24

Descriptions

Description	24X24X12 N4X SS CH CLMP CVR
extra long description	NVENT HOF A24H2412SS6LP Stainless E
Features	For use in indoor and outdoor corrosive environments that require a water-tight seal, this enclosure's seamless foam-in-place gasket and screw-down clamps provide a secure seal against contaminants.
Long Description	Wallmount Hinged with NEMA Clamps Type 4X, 24x24x12, Brushed, SS316
Product Type	Stainless Encl. 24.00X24.00X12
Short Description	Stainless Encl. 24.00x24.00x12

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510837709
Manufacturers Part Number	A24H2412SS6LP
UPC	783510837709

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Wall Mounted Industrial Enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5500 Wheeler Avenue
72901-0000, AR Fort Smith
Phone: 479-648-1902
Fax: 479-648-1960

Packaging

Carton	1
Weight Per each	59

Uses, Certifications, and Standards

Application	Controls and Drives;Corrosive Environments
nema rating	4X