



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A24R248HCR 24X24X8 N3R MD HC

Hoffman Enclosures, Inc.

Catalog Number	A24R248HCR
Manufacturer	Hoffman Enclosures, Inc.
Description	Medium Drip-Shield Hinged-Cover Type 3R, 24.00X24.00X8.00, Gray, Steel
Weight per unit	52.0 (lbs/each)
Product Category	Nema Types 3 & 3R Metallic Enc

Features

ip rating	IP32
Material	Steel

Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Galvanized

Dimensions and Weight

Depth	8
Height	24
Size	24.00x24.00x8.00 in
Width	24

Descriptions

Description	24X24X8 N3R MD HC
extra long description	NVENT HOF A24R248HCR Enclosure 24.0
Features	Medium Drip-Shield Hinged-Cover, Type 3R, protects wiring and other electrical components in outdoor applications that require protection from rain, sleet, snow or dripping water. It offers the flexibility of securing enclosure with an optional padlock and collar studs for optional panel mounting. These enclosures have a size range of 16 x 12 x 6-in. to 60 x 36 x 12-in.
Long Description	Medium Drip-Shield Hinged-Cover Type 3R, 24.00x24.00x8.00, Gray, Steel
Product Type	Enclosure 24.00X24.00X8.00
Short Description	Enclosure 24.00x24.00x8.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510387808
Manufacturers Part Number	A24R248HCR
UPC	783510387808



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures

Packaging

Carton	1
Weight Per each	52

Uses, Certifications, and Standards

Application	Controls and Drives;Power Distribution
nema rating	3R