

# Eaton A30CRE45BA5E045

Catalog Number: A30CRE45BA5E045

Eaton definite purpose 3-phase starter, Non-reversing, Common ctrl, Open w/ DIN rail mount adapter, Lugs w/o quick connect terms, 45 A, 208/240 V coil, 1NO pressure plate, Std. C440 OLR SEL reset, SEL class, 9-45 A overload



## General specifications

Product Name	Catalog Number
Eaton definite purpose starter	A30CRE45BA5E045
UPC	Product Length/Depth
786685955155	6.4 in
Product Height	Product Width
4.63 in	2.66 in
Product Weight	Warranty
1.6 lb	1 year
Certifications	
UL Listed	
CSA Certified	

## defaultTaxonomyAttributeLabel

### Current range

45 A

### Amperage Rating

208-240 V, 50/60 Hz

### Phase

Three-phase

### Type

Non-reversing

### Coil

208/240 Vac

### Contact configuration

1 NO pressure plate

### Control characteristics

Common control

### Enclosure

Open with DIN rail mounting adapter

### Inductive full load

45 A

### Overload range

9-45 A

### Terminals

Lugs without quick connect terms

### Model

Starter

### Olr model designation

SEL class

Std. C440 OLR SEL reset

## Resources

### Specifications and datasheets

Eaton Specification Sheet - A30CRE45BA5E045



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)