



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## A30H2412SSLP 30X24X12 4X Enclosure

*Hoffman Enclosures, Inc.*

Catalog Number	A30H2412SSLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Wallmount Hinged With Nema Clamps Type 4X, 30X24X12, Brushed, SS304
Weight per unit	69.0 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

### Features

ip rating	IP66
Material	Stainless Steel 304

### Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4

### Dimensions and Weight

Depth	12
Height	30
Size	30.00X24.00X12.00 in
Width	24

### Descriptions

Description	30X24X12 4X ENCLOSURE
extra long description	NVENT HOF A30H2412SSLP Stainless En
Features	For use in indoor and outdoor corrosive environments that require a water-tight seal, this enclosure's seamless foam-in-place gasket and screw-down clamps provide a secure seal against contaminants.
Long Description	Wallmount Hinged with NEMA Clamps Type 4X, 30x24x12, Brushed, SS304
Product Type	Stainless Encl. 30.00X24.00X12

### Manufacturer Information

Brand	Hoffman Enclosures, Inc.
Manufacturers Part Number	A30H2412SSLP

### Taxonomies, Classifications, and Categories

Type	Stainless Steel Wall Mounted Industrial Enclosures
------	--

### Packaging

Carton	1
Weight Per each	69



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Application .....	Corrosive Environments; Controls and Drives .....
nema rating .....	4X Watertight, corrosion-resistant .....