



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A30H2412SSLP 30X24X12 4X Enclosure

Hoffman Enclosures, Inc.

Catalog Number	A30H2412SSLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Wallmount Hinged With Nema Clamps Type 4X, 30X24X12, Brushed, SS304
Weight per unit	69.0 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

ip rating	IP66
Material	Stainless Steel 304

Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4

Dimensions and Weight

Depth	12
Height	30
Size	30.00x24.00x12.00 in
Width	24

Descriptions

Description	30X24X12 4X ENCLOSURE
extra long description	NVENT HOF A30H2412SSLP Stainless En
Features	For use in indoor and outdoor corrosive environments that require a water-tight seal, this enclosure's seamless foam-in-place gasket and screw-down clamps provide a secure seal against contaminants.
Long Description	Wallmount Hinged with NEMA Clamps Type 4X, 30x24x12, Brushed, SS304
Product Type	Stainless Encl. 30.00X24.00X12

Manufacturer Information

Brand	Hoffman Enclosures, Inc.
Manufacturers Part Number	A30H2412SSLP

Taxonomies, Classifications, and Categories

Type	Stainless Steel Wall Mounted Industrial Enclosures
------	--

Packaging

Carton	1
Weight Per each	69



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Corrosive Environments; Controls and Drives
nema rating	4X Watertight, corrosion-resistant