



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4509 Texoma Parkway  
75090-0000, TX Sherman  
Phone: 903-892-8041  
Fax: 903-892-8907



## A30H24BLP 30X24X8 N4 CH CLMP CVR

*Hoffman Enclosures, Inc.*

Catalog Number	A30H24BLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge Enclosure With Clamps LP Type 4, 30X24X8, Gray, Mild Steel
Weight per unit	58.0 (lbs/each)
Product Category	Nema Types 4 & 12 Metallic Enc

### Features

ip rating	IP66
Material	Steel

### Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Powder Coated

### Dimensions and Weight

Depth	8
Height	30
Size	30.00x24.00x8.00 in
Width	24

### Descriptions

Description	30X24X8 N4 CH CLMP CVR
extra long description	NVENT HOF A30H24BLP Type 4 Encl. 30
Features	These single-door enclosures feature a hinged door with clamps on three sides to create a secure seal in indoor or outdoor environments. The gray polyester powder finish inside and out provides enhanced corrosion protection in outdoor applications.
Long Description	Continuous Hinge Enclosure with Clamps LP Type 4, 30x24x8, Gray, Mild Steel
Product Type	Type 4 Encl. 30.00X24.00X8.00
Short Description	Type 4 Encl. 30.00x24.00x8.00

### Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510244705
Manufacturers Part Number	A30H24BLP
UPC	783510244705

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4509 Texoma Parkway  
75090-0000, TX Sherman  
Phone: 903-892-8041  
Fax: 903-892-8907

## Availability

Status ..... Inactive .....

## Packaging

Carton ..... 1 .....

Weight Per each ..... 58 .....

## Uses, Certifications, and Standards

Application ..... Controls and Drives .....

nema rating ..... 12 .....