



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4406 Highway 28 East
71360-0000, LA Pineville
Phone: 318-767-0900
Fax: 318-767-0010



A30H24DLP 30X24X12 N4 CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A30H24DLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge Enclosure With Clamps LP Type 4, 30X24X12, Gray, Mild Steel
Weight per unit	72.6 (lbs/each)
Product Category	Nema Types 4 & 12 Metallic Enc

Features

ip rating	IP66
Material	Steel

Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Powder Coated

Dimensions and Weight

Depth	12
Height	30
Size	30.00x24.00x12.00 in
Width	24

Descriptions

Description	30X24X12 N4 CH CLMP CVR
extra long description	NVENT HOF A30H24DLP Type 4 Encl. 30
Features	These single-door enclosures feature a hinged door with clamps on three sides to create a secure seal in indoor or outdoor environments. The gray polyester powder finish inside and out provides enhanced corrosion protection in outdoor applications.
Long Description	Continuous Hinge Enclosure with Clamps LP Type 4, 30x24x12, Gray, Mild Steel
Product Type	Type 4 Encl. 30.00X24.00X12.00
Short Description	Type 4 Encl. 30.00x24.00x12.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510245900
Manufacturers Part Number	A30H24DLP
UPC	783510245900

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4406 Highway 28 East
71360-0000, LA Pineville
Phone: 318-767-0900
Fax: 318-767-0010

Availability

Status Inactive

Packaging

Carton 1

Weight Per each 72.5999

Uses, Certifications, and Standards

Application Controls and Drives

nema rating 12