



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

801 Sterlington Rd.  
71203-0000, LA Monroe  
Phone: 318-387-1621  
Fax: 318-387-1763



## **A30HS2412GQRLP 30.25X24.25X12 N4X FG Discnct HC** *Hoffman Enclosures, Inc.*

Catalog Number	A30HS2412GQRLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Fiberglass Disconnect Type 4X, 30.25X24.25X12.00, LT Gray, Fiberglass
Weight per unit	46.0 (lbs/each)
Product Category	Nema Types 4, 4X, 12 & 13

### **Features**

ip rating	IP66
-----------	------

### **Material, Color, and Finish**

Color	Gray
Color Code	RAL 7035
Finish	Smooth Matte

### **Dimensions and Weight**

Depth	12
Height	30.25
Size	30.25x24.25x12.00 in
Width	24.25

### **Descriptions**

Description	30.25X24.25X12 N4X FG DISCNCT HC
extra long description	NVENT HOF A30HS2412GQRLP TYPE 4X DI
Features	For effective and economical disconnect protection in the harshest corrosive environments, these enclosures provide secure door closure through the use of Type 304 stainless steel slotted quarter-turn latches. Each Fiberglass Disconnect, Type 4X is furnished with bracket affixed to door for attaching disconnect door catch (interlock) and instructions for installing disconnect handle (handle not included).
Long Description	Fiberglass Disconnect Type 4X, 30.25x24.25x12.00, Lt Gray, Fiberglass
Product Type	Type 4X Disconnect Enclosure
Short Description	TYPE 4X DISCONNECT ENCLOSURE

### **Manufacturer Information**

Brand	Nvent Hoffman
GTIN	00783510132378
Manufacturers Part Number	A30HS2412GQRLP
UPC	783510132378



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

801 Sterlington Rd.  
71203-0000, LA Monroe  
Phone: 318-387-1621  
Fax: 318-387-1763

## Taxonomies, Classifications, and Categories

Type ..... Fiberglass Wall Mounted Industrial Disconnect Enclosures .....

## Packaging

Carton ..... 1 .....

Weight Per each ..... 46 .....

## Uses, Certifications, and Standards

Application ..... Arc Flash Safety;Controls and Drives;Corrosive Environments .....

nema rating ..... 4X .....