



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

310 Interstate Blvd
29615-0000, SC Greenville
Phone: 864-735-7911
Fax: 000-000-0000



A30HS2412GQRLP 30.25X24.25X12 N4X FG Discnct HC *Hoffman Enclosures, Inc.*

Catalog Number	A30HS2412GQRLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Fiberglass Disconnect Type 4X, 30.25X24.25X12.00, LT Gray, Fiberglass
Weight per unit	46.0 (lbs/each)
Product Category	Nema Types 4, 4X, 12 & 13

Features

ip rating	IP66
-----------	------

Material, Color, and Finish

Color	Gray
Color Code	RAL 7035
Finish	Smooth Matte

Dimensions and Weight

Depth	12
Height	30.25
Size	30.25x24.25x12.00 in
Width	24.25

Descriptions

Description	30.25X24.25X12 N4X FG DISCNCT HC
extra long description	NVENT HOF A30HS2412GQRLP TYPE 4X DI
Features	For effective and economical disconnect protection in the harshest corrosive environments, these enclosures provide secure door closure through the use of Type 304 stainless steel slotted quarter-turn latches. Each Fiberglass Disconnect, Type 4X is furnished with bracket affixed to door for attaching disconnect door catch (interlock) and instructions for installing disconnect handle (handle not included).
Long Description	Fiberglass Disconnect Type 4X, 30.25x24.25x12.00, Lt Gray, Fiberglass
Product Type	Type 4X Disconnect Enclosure
Short Description	TYPE 4X DISCONNECT ENCLOSURE

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510132378
Manufacturers Part Number	A30HS2412GQRLP
UPC	783510132378



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

310 Interstate Blvd
29615-0000, SC Greenville
Phone: 864-735-7911
Fax: 000-000-0000

Taxonomies, Classifications, and Categories

Type	Fiberglass Wall Mounted Industrial Disconnect Enclosures
------------	--

Packaging

Carton	1
--------------	---------

Weight Per each	46
-----------------------	----------

Uses, Certifications, and Standards

Application	Arc Flash Safety;Controls and Drives;Corrosive Environments
-------------------	---

nema rating	4X
-------------------	----------