



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

12555 Harris Branch Pkwy Suite 105
78653-0000, TX Manor
Phone: 512-339-8750
Fax: 512-339-6732



A363012LP 36X30X12 N4 CH Clamp CVR

Hoffman Enclosures, Inc.

Catalog Number	A363012LP
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge Enclosure With Clamps LP Type 4, 36X30X12, Gray, Mild Steel
Weight per unit	93.0 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Features

ip rating	IP66
Material	Steel

Material, Color, and Finish

Finish	Powder Coated
--------	---------------

Dimensions and Weight

Depth	12
Height	36
Size	36.00x30.00x12.00 in
Width	30

Descriptions

Description	36X30X12 N4 CH CLAMP CVR
extra long description	NVENT HOF A363012LP Enclosure 36.00
Features	These single-door enclosures feature a hinged door with clamps on three sides to create a secure seal in indoor or outdoor environments. The gray polyester powder finish inside and out provides enhanced corrosion protection in outdoor applications.
Long Description	Continuous Hinge Enclosure with Clamps LP Type 4, 36x30x12, Gray, Mild Steel
Product Type	Enclosure 36.00X30.00X12.00
Short Description	Enclosure 36.00x30.00x12.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510285401
Manufacturers Part Number	A363012LP
UPC	783510285401

Taxonomies, Classifications, and Categories

Type	Mild Steel Wall Mounted Industrial Enclosures
------	---

Packaging

Carton	1
Weight Per each	93



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

12555 Harris Branch Pkwy Suite 105
78653-0000, TX Manor
Phone: 512-339-8750
Fax: 512-339-6732

Uses, Certifications, and Standards

Application	Controls and Drives
nema rating	12