



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1308 North Nelson Street
79735-0000, TX Fort Stockton
Phone: 432-336-8730
Fax: 432-336-3279



A363612LP 36X36X12 N12 CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A363612LP
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge Enclosure With Clamps LP Type 4, 36X36X12, Gray, Mild Steel
Weight per unit	103.0 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Features

ip rating	IP66
Material	Steel

Material, Color, and Finish

Finish	Powder Coated
--------	---------------

Dimensions and Weight

Depth	12
Height	36
Size	36.00x36.00x12.00 in
Width	36

Descriptions

Description	36X36X12 N12 CH CLMP CVR
extra long description	NVENT HOF A363612LP Enclosure 36.00
Features	These single-door enclosures feature a hinged door with clamps on three sides to create a secure seal in indoor or outdoor environments. The gray polyester powder finish inside and out provides enhanced corrosion protection in outdoor applications.
Long Description	Continuous Hinge Enclosure with Clamps LP Type 4, 36x36x12, Gray, Mild Steel
Product Type	Enclosure 36.00X36.00X12.00
Short Description	Enclosure 36.00x36.00x12.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510279509
Manufacturers Part Number	A363612LP
UPC	783510279509

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures

Packaging

Carton	1
Weight Per each	103



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1308 North Nelson Street
79735-0000, TX Fort Stockton
Phone: 432-336-8730
Fax: 432-336-3279

Uses, Certifications, and Standards

Application	Controls and Drives
nema rating	12