



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## A36H2410SS6LP 36X24X10 N4X CH CLMP CVR

*Hoffman Enclosures, Inc.*

Catalog Number	A36H2410SS6LP
Manufacturer	Hoffman Enclosures, Inc.
Description	Wallmount Hinged With Nema Clamps Type 4X, 36X24X10, Brushed, SS316
Weight per unit	75.0 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

### Features

ip rating	IP66
Material	Stainless Steel;Stainless Steel 316L

### Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4

### Dimensions and Weight

Depth	10
Height	36
Size	36.00x24.00x10.00 in
Width	24

### Descriptions

Description	36X24X10 N4X CH CLMP CVR
extra long description	NVENT HOF A36H2410SS6LP Stainless E
Features	For use in indoor and outdoor corrosive environments that require a water-tight seal, this enclosure's seamless foam-in-place gasket and screw-down clamps provide a secure seal against contaminants.
Long Description	Wallmount Hinged with NEMA Clamps Type 4X, 36x24x10, Brushed, SS316
Product Type	Stainless Encl. 36.00X24.00X10
Short Description	Stainless Encl. 36.00x24.00x10

### Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510837303
Manufacturers Part Number	A36H2410SS6LP
UPC	783510837303

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Wall Mounted Industrial Enclosures



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	75

## Uses, Certifications, and Standards

Application	Controls and Drives; Corrosive Environments
nema rating	4X