



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A36H3012SSLP 36X30X12 N4X SS4 CH Clamp CVR

Hoffman Enclosures, Inc.

Catalog Number	A36H3012SSLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Wallmount Hinged With Nema Clamps Type 4X, 36X30X12, Brushed, SS304
Weight per unit	91.0 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

ip rating	IP66
Material	Stainless Steel;Stainless Steel 304

Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4

Dimensions and Weight

Depth	12
Height	36
Size	36.00x30.00x12.00 in
Width	30

Descriptions

Description	36X30X12 N4X SS4 CH CLAMP CVR
extra long description	NVENT HOF A36H3012SSLP Stainless En
Features	For use in indoor and outdoor corrosive environments that require a water-tight seal, this enclosure's seamless foam-in-place gasket and screw-down clamps provide a secure seal against contaminants.
Long Description	Wallmount Hinged with NEMA Clamps Type 4X, 36x30x12, Brushed, SS304
Product Type	Stainless Encl. 36.00X30.00X12
Short Description	Stainless Encl. 36.00x30.00x12

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510242206
Manufacturers Part Number	A36H3012SSLP
UPC	783510242206

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Wall Mounted Industrial Enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	91

Uses, Certifications, and Standards

Application	Controls and Drives; Corrosive Environments
nema rating	4X