



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9172 E Florentine Road Unit 9
86314-0000, AZ Prescott Valley
Phone: 928-356-1174
Fax: 480-426-8084



A36H30DLP 36X30X12 N4 CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A36H30DLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge Enclosure With Clamps LP Type 4, 36X30X12, Gray, Mild Steel
Weight per unit	95.0 (lbs/each)
Product Category	Nema Types 4 & 12 Metallic Enc

Features

ip rating	IP66
Material	Steel

Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Powder Coated

Dimensions and Weight

Depth	12
Height	36
Size	36.00x30.00x12.00 in
Width	30

Descriptions

Description	36X30X12 N4 CH CLMP CVR
extra long description	NVENT HOF A36H30DLP Type 4 Encl. 36
Features	These single-door enclosures feature a hinged door with clamps on three sides to create a secure seal in indoor or outdoor environments. The gray polyester powder finish inside and out provides enhanced corrosion protection in outdoor applications.
Long Description	Continuous Hinge Enclosure with Clamps LP Type 4, 36x30x12, Gray, Mild Steel
Product Type	Type 4 Encl. 36.00X30.00X12.00
Short Description	Type 4 Encl. 36.00x30.00x12.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510246006
Manufacturers Part Number	A36H30DLP
UPC	783510246006

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9172 E Florentine Road Unit 9
86314-0000, AZ Prescott Valley
Phone: 928-356-1174
Fax: 480-426-8084

Availability

Status Inactive

Packaging

Carton 1

Weight Per each 95

Uses, Certifications, and Standards

Application Controls and Drives

nema rating 12