



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

903 Mississippi Ave  
76301-0000, TX Wichita Falls  
Phone: 940-257-6832  
Fax: 940-257-6833



## A36H3612SS6LP 36X36X12 N4X SS6 CH CLMP CVR

*Hoffman Enclosures, Inc.*

Catalog Number	A36H3612SS6LP
Manufacturer	Hoffman Enclosures, Inc.
Description	Wallmount Hinged With Nema Clamps Type 4X, 36X36X12, Brushed, SS316
Weight per unit	105.0 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

### Features

ip rating	IP66
Material	Stainless Steel;Stainless Steel 316L

### Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4

### Dimensions and Weight

Depth	12
Height	36
Size	36.00x36.00x12.00 in
Width	36

### Descriptions

Description	36X36X12 N4X SS6 CH CLMP CVR
extra long description	NVENT HOF A36H3612SS6LP Stainless E
Features	For use in indoor and outdoor corrosive environments that require a water-tight seal, this enclosure's seamless foam-in-place gasket and screw-down clamps provide a secure seal against contaminants.
Long Description	Wallmount Hinged with NEMA Clamps Type 4X, 36x36x12, Brushed, SS316
Product Type	Stainless Encl. 36.00X36.00X12
Short Description	Stainless Encl. 36.00x36.00x12

### Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510837907
Manufacturers Part Number	A36H3612SS6LP
UPC	783510837907

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Wall Mounted Industrial Enclosures



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

903 Mississippi Ave  
76301-0000, TX Wichita Falls  
Phone: 940-257-6832  
Fax: 940-257-6833

## Packaging

Carton	1
Weight Per each	105

## Uses, Certifications, and Standards

Application	Controls and Drives; Corrosive Environments
nema rating	4X