Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

A4424RT 4X4X24 N3R SC Wire Trough

Hoffman Enclosures, Inc.

Catalog Number	A4424RT
Manufacturer	Hoffman Enclosures, Inc.
Description	Wiring Trough Nema Type 3R, 4.00X4.00X24.00, Gray, Steel
Weight per unit	9.3 (lbs/each)
Product Category	Nema Type 3R Trough & Gutter

Features

ip rating	IP32
Material	Mild Steel;Steel

Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Galvanized

Dimensions and Weight

Depth	24
Size	4.00x4.00x24.00 in
Width	4

Descriptions

Description	4X4X24 N3R SC WIRE TROUGH
extra long description	NVENT HOF A4424RT Trough Wire NEMA
Features	Screw-Cover Wiring Trough, Type 3R is used for protecting wire and cable distribution, junctions and terminations in outdoor applications that may be exposed to wet conditions. A Padlock Hasp Kit can be installed for increased security.
Long Description	Wiring Trough NEMA Type 3R, 4.00x4.00x24.00, Gray, Steel
Product Type	Trough Wire Nema Type 3R Gy MS 4X4X24
Short Description	Wiring Trough 4.00x4.00x24.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510382100
Manufacturers Part Number	A4424RT
UPC	783510382100

Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	Commercial Wiring Troughs;Trough

Packaging

Carton	1
Weight Per each	9.29

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Power Distribution
nema rating	3R Weather-resistant, except dust