



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 W. Esthner Avenue  
67213-0000, KS Wichita  
Phone: 316-854-0028  
Fax: 316-854-0029



## **A48H3612GQRLP 48.25X36.25X12 N4X FG QK RLS HC** *Hoffman Enclosures, Inc.*

Catalog Number	A48H3612GQRLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Hinge Cover Enclosure Quick-Release Type 4X, 48.25X36.25X12.00, Gray, Fiberglass
Weight per unit	77.0 (lbs/each)
Product Category	Nema Types 4, 4X, 12 & 13

### **Features**

ip rating	IP66
-----------	------

### **Material, Color, and Finish**

Color	Gray
Finish	Smooth Matte

### **Dimensions and Weight**

Depth	12
Height	48.25
Size	48.25x36.25x12.00 in
Width	36.25

### **Descriptions**

Description	48.25X36.25X12 N4X FG QK RLS HC
extra long description	NVENT HOF A48H3612GQRLP Enclosure 4
Features	A full range of modification options are available for wall-mount fiberglass enclosures, including variable depths to accommodate larger controls. These enclosures feature padlockable polyester latches, or HOFFMAN's exclusive PowerGlide Handle with 3-point latching, for ease of access with increased security.
Long Description	Hinge Cover Enclosure Quick-Release Type 4X, 48.25x36.25x12.00, Gray, Fiberglass
Product Type	Enclosure 48.25X36.25X12.00
Short Description	Enclosure 48.25x36.25x12.00

### **Manufacturer Information**

Brand	Nvent Hoffman
GTIN	00783510227401
Manufacturers Part Number	A48H3612GQRLP
UPC	783510227401

### **Taxonomies, Classifications, and Categories**

Category Description	VYNCKIER FIBERGLASS ENCLOSURES
Type	Fiberglass and Thermoplastic Wall Mounted Industrial Enclosures



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 W. Esthner Avenue  
67213-0000, KS Wichita  
Phone: 316-854-0028  
Fax: 316-854-0029

## Packaging

Carton	1
Weight Per each	77

## Uses, Certifications, and Standards

Application	Controls and Drives;Corrosive Environments
nema rating	4X