



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

13405 Stemmons Frwy
75234-0000, TX Farmers Branch
Phone: 972-206-0016
Fax: 972-352-2818



A512H 12 Hour Twist Timer Ivory

Nsi Industries

Catalog Number	A512H
Manufacturer	Nsi Industries
Description	The Tork A512H 12-Hour Spring-Wound In-Wall Twist Timer Is Designed to Control A Variety Of Indoor Appliances and Lights. Automate Your Home or Office to Save Energy and Money Using The Simple Twist Knob and Reliable Mechanical Timekeeping. Features A Time Range Of 30 Minutes to 12 Hours, Plus It Fits Into A Standard Electrical Box For In-Wall Mounting. Designed For Indoor Loads Such As Lights, Whole House Fans, Air Compressors, Water Heaters or Motors.
Weight per unit	0.3240 (lbs/each)
Product Category	Electromechanical Time Switches

Features

action	SPDT
Base	Wall Plate
Contact Rating	125-250-277 VAC
Phase	Single Phase
Poles	1
Timing Range	12 Hour

Dimensions and Weight

Size	H=5.00 - W=3.00
------	-----------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

13405 Stemmons Frwy
75234-0000, TX Farmers Branch
Phone: 972-206-0016
Fax: 972-352-2818

Descriptions

Description	12 HOUR TWIST TIMER IVORY
extra long description	TORK A512H 12 Hour Spring Wound Twi
Features	The TORK A512H spring-wound in-wall twist timer carries our legacy of innovation and quality with reliable timekeeping and consistent performance. Use twist timers to set a countdown for automatically shutting off appliances or lighting, saving you energy and trouble. No more forgetting to turn off a garage light or attic fan: with a twist timer, simply wind the knob to the correct duration and automate the process. TORK twist timers are at home in residential environments or a range of commercial applicat
Long Description	The TORK A512H 12-Hour Spring-Wound In-Wall Twist Timer is designed to control a variety of indoor appliances and lights. Automate your home or office to save energy and money using the simple twist knob and reliable mechanical timekeeping. Features a time range of 30 minutes to 12 hours, plus it fits into a standard electrical box for in-wall mounting. Designed for indoor loads such as lights, whole house fans, air compressors, water heaters or motors.
Product Type	12 Hour Spring Wound Twist Timer 125-277V SPDT Ivory
Special Features	Ivory 12 Hour No Hold In Wall Time Switch

Manufacturer Information

Brand	TORK
GTIN	00786261150196
Manufacturers Part Number	A512H
UPC	786261150196

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Spring Wound In Wall Time Switch

Packaging

Carton	1
Weight Per each	0.324



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

13405 Stemmons Frwy
75234-0000, TX Farmers Branch
Phone: 972-206-0016
Fax: 972-352-2818

Uses, Certifications, and Standards

Application	NSI
Enclosure	Single Gang Wall Plate
environmental conditions	32-122 F
Frequency Rating	50-60 Hz
Mounting	Single Gang Wall Plate
Operating Temperature	32-122 F
standard	cULus