

Standard Length – Reels

Size	Color	Part No.	Nom I.D.	Nom O.D.	Pull Tape	Reel Size	Reel length (ft.)	Prod. Wt. per 100 ft. (lbs.)
1"	Orange	A5D2S1JNNB1000	1.049	1.340	1130 lb.	48-30-24	1000	12.5
	Orange	A5D2S1JNNB1800	1.049	1.340	1130 lb.	48-30-24	1800	12.5
	Orange	A5D2S1JNNB2000	1.049	1.340	1130 lb.	48-41-24	2000	12.5
	Orange	A5D2S1JNNB2700	1.049	1.340	1130 lb.	48-41-24	2700	12.5
	Orange	A5D2S1JNNB5000	1.049	1.340	1130 lb.	66-41-24	5000	12.5
	Orange	A5D2S1JNNB6500	1.049	1.340	1130 lb.	72-41-24	6500	12.5
	Orange	A5D2S1JNNB7000	1.049	1.340	1130 lb.	72-45-24	7000	12.5
1 1/4"	Orange	A6D2S1JNNB1000	1.250	1.565	1130 lb.	48-30-24	1000	14.4
	Orange	A6D2S1JNNB1600	1.250	1.565	1130 lb.	48-41-24	1600	14.4
	Orange	A6D2S1JNNB2500	1.250	1.565	1130 lb.	66-41-24	2500	14.4
	Orange	A6D2S1JNNB4000	1.250	1.565	1130 lb.	66-41-24	4000	14.4
	Orange	A6D2S1JNNB5000	1.250	1.565	1130 lb.	72-41-24	5000	14.4
	Orange	A6D2S1JNNB6000	1.250	1.565	1130 lb.	82-41-24	6000	14.4
	Orange	A6D2S1JNNB7000	1.250	1.565	1130 lb.	84-45-24	7000	14.4
1 1/2"	Orange	A9D2S1JNNB1000	1.500	1.825	1130 lb.	66-41-24	1000	17.8
	Orange	A9D2S1JNNB2200	1.500	1.825	1130 lb.	66-41-24	2200	17.8
	Orange	A9D2S1JNNB2900	1.500	1.825	1130 lb.	72-41-24	2900	17.8
	Orange	A9D2S1JNNB4000	1.500	1.825	1130 lb.	82-41-24	4000	17.8
2"	Orange	A13D2S1JNNB500	2.000	2.425	1130 lb.	48-30-24	500	25.0
	Orange	A13D2S1JNNB750	2.000	2.425	1130 lb.	48-41-24	750	25.0
	Orange	A13D2S1JNNB1000	2.000	2.425	1130 lb.	66-41-24	1000	25.0
	Orange	A13D2S1JNNB1500	2.000	2.425	1130 lb.	66-41-24	1500	25.0
	Orange	A13D2S1JNNB1800	2.000	2.425	1130 lb.	72-41-24	1800	25.0
	Orange	A13D2S1JNNB2000	2.000	2.425	1130 lb.	82-41-24	2000	25.0

Standard Length – Coils

Size	Color	Part No.	Nom I.D.	Nom O.D.	Pull Tape	Box Size	Reel length (ft.)	Prod. Wt. per 100 ft. (lbs.)
1"	Orange	A5D2E1JNNA250	1.049	1.340	Empty	COIL	250/Split	12.5
	Orange	A5D2E1JNNA250B	1.049	1.340	Empty	34-14-34	250/Split	12.5
	Orange	A5D2S1JNNB250	1.049	1.340	1130 lb.	COIL	250	12.5
	Orange	A5D2S1JNNB250B	1.049	1.340	1130 lb.	34-14-34	250	12.5
	Orange	A5D2S1JNNB500	1.049	1.340	1130 lb.	COIL	500	12.5
	Orange	A5D2S1JNNB500B	1.049	1.340	1130 lb.	39-15-39	500	12.5
1 1/4"	Orange	A6D2E1JNNA250	1.250	1.565	Empty	COIL	250/Split	14.4
	Orange	A6D2E1JNNA250B	1.250	1.565	Empty	39-15-39	250/Split	14.4
	Orange	A6D2S1JNNB250	1.250	1.565	1130 lb.	COIL	250	14.4
	Orange	A6D2S1JNNB250B	1.250	1.565	1130 lb.	39-15-39	250	14.4
	Orange	A6D2S1JNNB500	1.250	1.565	1130 lb.	COIL	500	14.4
	Orange	A6D2S1JNNB500B	1.250	1.565	1130 lb.	44-18-44	500	14.4
1 1/2"	Orange	A9D2S1JNNB250	1.500	1.825	1130 lb.	COIL	250	17.8
	Orange	A9D2S1JNNB250B	1.500	1.825	1130 lb.	44-18-44	250	17.8
	Orange	A9D2S1JNNB500	1.500	1.825	1130 lb.	COIL	500	17.8
2"	Orange	A13D2S1JNNB250	2.000	2.425	1130 lb.	COIL	250	25.0

Custom Orders

* Custom Orders are not returnable

* Custom lengths are available in minimum order quantities. See Quote form.

How to Build a Part Number:

Position 1 Product	Position 2 Size	Position 3 Type	Position 4 Wall	Position 5 Options	Position 6 Splits	Position 7 Color	Position 8 Stripes	Position 9 Tape	Position 10 Length
A = HDPE	5 = 1" 6 = 1-1/4" 9 = 1-1/2" 13 = 2"	D = Corrugated	2 = None - Corr	N = None - Custom E = Slit S = Standard Length	1 = 1 Way Single 2 = 2 Way Segmented 3 = 3 Way Segmented 4 = 4 Way Segmented 5 = 2 Way Parallel 6 = 3 Way Parallel 7 = 4 Way Parallel	A = Black B = Blue C = Brown D = Buff E = Grey F = Green G = Lilac H = Lt. Green J = Orange K = Red L = Terra Cotta M = White N = Yellow	NN = None 1A = Black Stripe 1B = Blue Stripe 1C = Brown Stripe 1D = Buff Stripe 1E = Grey Stripe 1F = Green Stripe 1G = Lilac Stripe 1H = Lt. Green Stripe 1J = Orange Stripe 1K = Red Stripe 1L = Terra Cotta Stripe 1M = White Stripe 1N = Yellow Stripe	A = Empty B = 1130 lbs. Polyester Tape C = 1250 lbs. Polyester Tape E = 1800 lbs. Polyester Tape G = 200 lbs. Polyester Tape J = 2500 lbs. Polyester Tape	1500 (Equals 1500 Feet)