



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A80 80 CFM 2.0 Sones Fan

Broan/Nutone LLC

Catalog Number	A80
Manufacturer	Broan/Nutone LLC
Description	Ventilation Fan, Rugged 26 Gauge Galvanized Steel, Ceiling Mount, 120 V Ac @ 60 HZ, 43.1 W, 0.37 A, 80 CFM Air Flow, 60 HZ, Round Duct Shape, 4 In Duct Size, White, Polymeric Grill Material, Rectangular Grill Shape, 11-3/8 In (L) X 12 In (W) Grill Size, Rugged 26 Gauge Galvanized Steel Housing Material, Rectangular Housing Shape, Permanently Lubricated Plug-In Motor, 9-1/4 In Overall Length, 10 In Overall Width, 5-3/4 In Overall Height, 4 In Duct Diameter, Exhaust, 8.75 LB
Weight per unit	8.8 (lbs/each)
Product Category	Exhaust Fans

Features

Air Flow Rate	80 CFM
Sound Level	2 SONES
Ventilation Area	75 Square Foot

Dimensions and Weight

Size	9-1/4 Inch Length x 10 Inch Width x 5-3/4 Inch Height
------	---

Descriptions

Additional Information	Power Rating 43.1 Watt; Efficacy Rating 1.89 CFM/Watt; Duct Direction Horizontal; Includes Permanently Lubricated Plug-In Motor, Blower Wheel
Commodity Description	Exhaust Fans
Description	80 CFM 2.0 SONES FAN

Manufacturer Information

GTIN	00026715236510
UPC	026715236510

Taxonomies, Classifications, and Categories

Category Description	FANS & HEATERS
Type	Ceiling, 1-Speed

Packaging

Carton	1
Weight Per each	8.75

Uses, Certifications, and Standards

Approval	UL, HVI
----------	---------