



Powering Business Worldwide

pe.eaton.com

Fast-Acting Fuse

ABC-3-R

UPC:051712646246

Dimensions:

- **Height:** .25 IN
- **Length:** 1.25 IN
- **Width:** .25 IN

Weight:.004 LB

Notes:Ceramic body allows for higher amp/volt rating combinations.

Warranties: No Data

Specifications:

- **Type:** Electronic
- **Application:** Electronic circuits
- **Amperage Rating:** 3A
- **Voltage Rating:** 250 Vac, 125 Vdc, 32 Vac (self certified)
- **Interrupt Rating:** 100 AIC at 250 Vac, 10 kAIC at 125 Vac/dc
- **Fuse Indicator:** Non Indicating
- **Packaging Type:** Standard
- **Response Time:** 4 hr minimum at 100%, 60 min maximum at 135%, 120 s maximum at 200%
- **Voltage Drop:** Typical: .14 mV
- **Melting (L2T):** Typical pre-arc: 6.55
- **Diameter:** .25 IN
- **Material:** Ceramic tube, nickel-plated brass endcaps
- **Connection:** Ferrule end X ferrule end
- **Resistance:** Typical DC cold: .047 ohms

Supporting documents:

- [ABC 3A BUSS FA 5-IN BOX -R](#)

Certifications: No Data



Product compliance:

- CE Marked
- RoHS Compliant

© 2016 Eaton. All rights reserved.