Specifications



Photo is representative





Eaton ABC-5-R

Eaton GBB Series Very fast-acting fuse, 12A, 250 Vac, 125 Vdc

General specifications		
PRODUCT NAME	Eaton Bussmann series ABC fast-acting fuse	
CATALOG NUMBER	ABC-5-R	
UPC	051712646284	
PRODUCT HEIGHT	32 mm	
PRODUCT DIAMETER	6.4 mm	
PRODUCT WEIGHT	2.05 g	
COMPLIANCES	CE Marked RoHS Compliant	
CATALOG NOTES	Ceramic body allows for higher amp/volt rating combinations.	



Product specifications		
AMPERAGE RATING	5 A	
MELTING (I2T)	Typical pre-arc: 32.83	
RESISTANCE	0.026 ohms DC cold	
VOLTAGE DROP	0.22 mV typical	
INTERRUPT RATING	200 AIC at 250 Vac 10 kAIC at 125 Vac/dc	
FUSE INDICATOR	Non-indicating	
CONNECTION	Ferrule end x ferrule end	
RESPONSE TIME	4 hr at 100%, 60 min at 135%, 120 sec at 200%	
MATERIAL	Ceramic tube Nickel-plated brass endcaps	
QUANTITY	5	
VOLTAGE RATING	250 Vac, 125 Vdc, 32 Vac (self certified)	
ТҮРЕ	Electronic	
APPLICATION	Electronic circuits	

Resources	
PEP ECO-PASSPORT	EATO-00033-V01.01-EN
SPECIFICATIONS AND DATASHEETS	Eaton ABC fast-acting ceramic tube fuses data sheet
DATAGREETS	<u>Eaton Specification Sheet -</u> <u>ABC-5-R</u>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com



information.



latest product and support

Follow us on social media to get the





Specifications



Photo is representative





Eaton ABC-5-R

Eaton GBB Series Very fast-acting fuse, 12A, 250 Vac, 125 Vdc

General specifications		
PRODUCT NAME	Eaton Bussmann series ABC fast-acting fuse	
CATALOG NUMBER	ABC-5-R	
UPC	051712646284	
PRODUCT HEIGHT	32 mm	
PRODUCT DIAMETER	6.4 mm	
PRODUCT WEIGHT	2.05 g	
COMPLIANCES	CE Marked RoHS Compliant	
CATALOG NOTES	Ceramic body allows for higher amp/volt rating combinations.	



Product specifications		
AMPERAGE RATING	5 A	
MELTING (I2T)	Typical pre-arc: 32.83	
RESISTANCE	0.026 ohms DC cold	
VOLTAGE DROP	0.22 mV typical	
INTERRUPT RATING	200 AIC at 250 Vac 10 kAIC at 125 Vac/dc	
FUSE INDICATOR	Non-indicating	
CONNECTION	Ferrule end x ferrule end	
RESPONSE TIME	4 hr at 100%, 60 min at 135%, 120 sec at 200%	
MATERIAL	Ceramic tube Nickel-plated brass endcaps	
QUANTITY	5	
VOLTAGE RATING	250 Vac, 125 Vdc, 32 Vac (self certified)	
ТҮРЕ	Electronic	
APPLICATION	Electronic circuits	

Resources	
PEP ECO-PASSPORT	EATO-00033-V01.01-EN
SPECIFICATIONS AND DATASHEETS	Eaton ABC fast-acting ceramic tube fuses data sheet
DATAGREETS	<u>Eaton Specification Sheet -</u> <u>ABC-5-R</u>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com



information.



latest product and support

Follow us on social media to get the



