

# Specifications



Photo is representative



## Eaton ABC-6-R

Eaton AGC series Fast-acting fuse, 8A, 250 Vac, 32 Vdc (self certified)

### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series ABC fast-acting fuse
<b>CATALOG NUMBER</b>	ABC-6-R
<b>UPC</b>	051712646291
<b>PRODUCT HEIGHT</b>	32 mm
<b>PRODUCT DIAMETER</b>	6.4 mm
<b>PRODUCT WEIGHT</b>	2.05 g
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CATALOG NOTES</b>	Ceramic body allows for higher amp/volt rating combinations.



Powering Business Worldwide

## Product specifications

AMPERAGE RATING	6 A
MELTING (I2T)	Typical pre-arc: 58
RESISTANCE	0.021 ohms DC cold
VOLTAGE DROP	0.19 mV typical
INTERRUPT RATING	200 AIC at 250 Vac 10 kAIC at 125 Vac/dc
FUSE INDICATOR	Non-indicating
CONNECTION	Ferrule end x ferrule end
RESPONSE TIME	4 hr at 100%, 60 min at 135%, 120 sec at 200%
MATERIAL	Ceramic tube Nickel-plated brass endcaps
QUANTITY	5
VOLTAGE RATING	250 Vac, 125 Vdc, 32 Vac (self certified)
TYPE	Electronic
APPLICATION	Electronic circuits

## Resources

PEP ECO-PASSPORT	<a href="#">EATO-00033-V01.01-EN</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - ABC-6-R</a>
	<a href="#">Eaton ABC fast-acting ceramic tube fuses data sheet</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

