

# 902 True-rms HVAC Clamp Meter



## AC72 Alligator Clip Set

Item #1670095

- Slide-on alligator clips (red, black) for TL71/TL75
- Jaws provide 8 mm opening
- CAT IV 600 V, CAT III 1000 V, 10 A rating. UL listed
- One-year warranty



## 80AK-A Thermocouple Adapter

Item #2747812

- Adapts Type-K thermocouple mini-connector to shrouded dual banana plug inputs
- Measurement range and accuracy: probe dependent
- Suitable for low voltage applications (below 30 V AC, 60 V DC)
- One-year warranty



## 80PK-8 Pipe Clamp Temperature Probe

Item #200360

- Type-K thermocouple for fast temperature and superheat measurements of pipe surfaces
- Durable ribbon sensor
- Measurement range: -29 °C to 149 °C for pipe diameters from 6.4 mm to 34.9 mm
- One-year warranty

